

Email :
sales@schooleducationalinstruments.com
Phone: +91-0171-2601773

Product Name :
Angular Measurement Trainers

Product Code :
SCHOOL-MES880001



Description :

Angular Measurement Trainers

Technical Specification :

The Trainer helps to studies Study of a Stroboscope. Measurement of Angular Speed (RPM). Mini DC motor with speed control arrangement. Strobe signal generator with frequency display. Strobe light Generator arrangement. Strobe light Frequency meter (digital). The Trainer complete with: DC power supply for application circuit. Reflector fitted with motor shaft. FEATURES: DC power supply for application circuit. Reflector fitted with motor shaft. Mini DC motor with speed control arrangement. Strobe signal generator with frequency display. Closed black box Thick pinewood closed cabinet. Complete operating & Experimental manual SPECIFICATION: Servo potentiometer as angular displacement measurement transducer (full 0-3600) using calibrated dial with 2° resolution Linear potentiometer as linear displacement measurement transducer (0-100mm) using mechanical attachment with vernier 5 digit DPM to read displacement Constant calibrated Interconnection: 2/4 mm banana sockets Op amp in signal conditioner circuit Offset adder for position modulation DC Supply: Built in IC regulated power supply Enclosed in an attractive ABS plastic cabinet with cover Accessories: Users Manual with patch cords Power required for operation 230V, 50Hz, 1 phase 230V, 60Hz, 1 phase

Website: [www.https://www.schooleducationalinstruments.com/](https://www.schooleducationalinstruments.com/), **Email:** sales@schooleducationalinstruments.com

Address: Ambala Cantt, Haryana, India **Phone:** 91-0171-2643080

NAUGRA[®]