

Email :
sales@schooleducationalinstruments.com
Phone: +91-0171-2601773

Product Name :
Flex Turn CNC Lathe

Product Code :
SCHOOL-CAD890005



Description :

Flex Turn CNC Lathe

Technical Specification :

FEATURES:

For specific application like slot milling, face drilling/threading, profile contouring, one separate set of live tools are provided with independent servomotor and drive.

All these features combined on this CNC chucker machine provide unsurpassed manufacturing speed and accuracy.

SPECIFICATION:

Chuck Capacity: 100 mm

Maximum Turning Diameter: 80 mm

Maximum Turning Length: 190 mm

Positioning Accuracy: 0.01 mm

Spindle Nose Taper Nos.: A2-3/MT3

Hole Through Spindle: 20 mm

Of Stations: 8 Nos.

X/Z Axis Travel: 95/210 mm

Rapid X/Z: 5000 mm/min

Feed Rate: 0-5000 mm/min

Tailstock Base Stroke: 170 mm

Spindle Speed Range: 150-4000 RPM

Spindle Motor: 3.7 KW

Quill Stroke: 40 mm

Quill Diameter: 35 mm

Tail Stroke Taper: MT2 MT 2

NAUGRA[®]

School Educational Instruments

Website: [www.https://www.schooleducationalinstruments.com/](https://www.schooleducationalinstruments.com/), **Email:** sales@schooleducationalinstruments.com

Address: Ambala Cantt, Haryana, India **Phone:** 91-0171-2643080